

Monostable Multivibrator Dual-Element 0°C 70°C 16-Pin SOIC T/R

Manufacturer:	Texas Instruments, Inc	<input type="text" value="SN74LS123DR Image"/>
Package/Case:	SOP16	Images are for reference only
Product Type:	Logic ICs	<input type="button" value="Inquiry"/>
RoHS:	RoHS Compliant/Lead free 	
Lifecycle:	Active	

General Description

These d-c triggered multivibrators feature output pulse-duration control by three methods. The basic pulse time is programmed by selection of external resistance and capacitance values (see typical application data). The '122 and 'LS122 have internal timing resistors that allow the circuits to be used with only an external capacitor, if so desired. Once triggered, the basic pulse duration may be extended by retriggering the gated low-level-active (A) or high-level-active (B) inputs, or be reduced by use of the overriding clear. Figure 1 illustrates pulse control by retriggering and early clear.

The 'LS122 and 'LS123 are provided enough Schmitt hysteresis to ensure jitter-free triggering from the B input with transition rates as slow as 0.1 millivolt per nanosecond.

The Rint is nominally 10 k for '122 and 'LS122.

Key Features

D-C Triggered from Active-High or Active-Low Gated Logic Inputs

Retriggerable for Very Long Output Pulses, Up to 100% Duty Cycle

Overriding Clear Terminates Output Pulse


'122 and 'LS122 Have Internal Timing Resistors

Description

These d-c triggered multivibrators feature output pulse-duration control by three methods. The basic pulse time is programmed by selection of external resistance and capacitance values (see typical application data). The '122 and 'LS122 have internal timing resistors that allow the circuits to be used with only an external capacitor, if so desired. Once triggered, the basic pulse duration may be extended by retriggering the gated low-level-active (A) or high-level-active (B) inputs, or be reduced by use of the overriding clear. Figure 1 illustrates pulse control by retriggering and early clear.

The 'LS122 and 'LS123 are provided enough Schmitt hysteresis to ensure jitter-free triggering from the B input with transition rates as slow as 0.1 millivolt per nanosecond.

The Rint is nominally 10 k for '122 and 'LS122.



Recommended For You

SN74S38N

Texas Instruments, Inc

DIP

SN7438N

Texas Instruments, Inc

DIP14

SN75462P

Texas Instruments, Inc

DIP8

SN74F08D

Texas Instruments, Inc

SOP-14

SN74LS257BN

Texas Instruments, Inc

DIP16

SN75452BP

Texas Instruments, Inc

DIP8

SN74LS245DW

Texas Instruments, Inc

SOP20

SN74LS74AN

Texas Instruments, Inc

DIP

SN74S74N

Texas Instruments, Inc

DIP

SN7406N

Texas Instruments, Inc

DIP-14

SN74CBILV3257D

Texas Instruments, Inc

SOP-16P

SN74HC138DR

Texas Instruments, Inc

SOP16

SN74LS14N

Texas Instruments, Inc

DIP

SN74HC139N

Texas Instruments, Inc

DIP

SN74AVC16T245DGGR

Texas Instruments, Inc

TSSOP48